

FR055WA05 2" / FR084WA03 3¼" 64 ohm fullranges for Line Arrays

The two 64 ohm fullrange transducers FR055WA05 (2") and FR084WA03 (3.25") share same design ideas, performance targets, and applications. Both were designed for high quality Line Arrays, with 8 transducers connected in parallel (8 ohm system impedance), or 16 in parallel for 4 ohm system impedance.

FEATURES

- True full-range designs with on-axis output to beyond 20 kHz
- Copper cap on center pole to reduce voice coil inductance and to minimize variations in voice coil inductance as a function of voice coil position (FR084WA03 only)
- Black anodized alu cone for better heat transfer
- Vented polymer chassis for lower air flow speed reducing audible distortion
- Vented voice coil former for reduced distortion and compression
- Heavy-duty black fiber glass voice coil bobbin to reduce mechanical losses resulting in better dynamic performance and low-level details
- Large motor with 22 mm voice coil diameter for better control and power handling
- Low-loss suspension (high Qm) for better reproduction of details and dynamics
- ٠ Black motor parts for better heat transfer to the surrounding air
- Conex spider for better durability under extreme conditions
- Gold plated terminals to ensure long-term trouble free connection Delivered with foam gasket attached for hassle-free mounting and secure cabinet
- sealingdetails and dynamics
- Black motor parts for better heat transfer to the surrounding air
- Conex spider for better durability under extreme conditions Gold plated terminals to ensure long-term trouble free connection

FR055WA05



2" fullrange, 64 ohm

3¼" fullrange, 64 ohm FR084WA03



NOMINAL SPECIFICATIONS

Notes	Parameter	FR055WA05 2" 64 ohm		FR084WA03 3¼" 64 ohm		Unit
Notes		Before burn-in	After burn-in	Before burn-in	After burn-in	Unit
	Nominal size		2	3	1/4	[inch.]
	Nominal impedance	6	64	6	54	[ohm]
	Recommended max. upper frequency limit	full r	ange	full range		[kHz]
1, 4	Sensitivity, 2.83V/1m	7	0	74		[dB]
2, 4	Power handling, short term, IEC 268-5, no additional filtering	40 30		30	[W]	
2, 4	Power handling, long term, IEC 268-5, no additional filtering	20 25		25	[W]	
2, 4	Power handling, continuous, IEC 268-5, no additional filtering	4		10		[W]
	Effective radiating area, Sd	15	5.6	3	38	[cm ²]
3, 4, 6	Resonance frequency (free air, no baffle), F _S	149	135	120	116	[Hz]
	Moving mass, incl. air (free air, no baffle), Mms	1.	45	3.	05	[g]
3, 4	Force factor, Bxl	5.5		6.8		[N/A]
3, 4, 6	Suspension compliance, Cms	0.785	0.96	0.58	0.62	[mm/N]
3, 4, 6	Equivalent air volume, V _{as}	0.27	0.33	1.07	1.14	[lit.]
3, 4, 6	Mechanical resistance, Rms	0.16	0.16	0.30	0.30	[Ns/m]
3, 4, 6	Mechanical Q, Qms	8.5	7.7	7.6	7.4	[-]
3, 4, 6	Electrical Q, Qes	2.37	2.14	2.43	2.35	[-]
3, 4, 6	Total Q, Qts	1.85	1.67	1.94	1.78	[-]
4	Voice coil resistance, RDC	53.5		49		[ohm]
5	Voice coil inductance, Le (measured at 10 kHz)	0.64		0.63		[mH]
	Voice coil inside diameter	22		22		[mm]
	Voice coil winding height	4.7		8		[mm]
	Air gap height	2		3		[mm]
	Theoretical linear motor stroke, Xmax	±1.35		±2.5		[mm]
	Magnet type	Dual neodymium		Ferrite		[-]
	Magnet weight	19		160		[g]
	Total unit net weight excl. packaging	0.071		0.37		[kg]
3, 4, 5	Krm					[mohm]
3, 4, 5	Erm					[-]
3, 4, 5	K _{xm}					[mH]
3, 4, 5	Exm					[-]

Measured in infinite baffle. Note 1


Tested in free air (no cabinet). Note 2

Note 3 Note 4 Measured using a semi-constant current source, nominal level 2 mA. Measured at 25 deg. C

It is generally a rough simplification to assume that loudspeaker transducer voice coils exhibit the characteristics of an inductor. Instead it is a far more accurate approach to use the more advanced model often referred to as the "Wright empirical model", also used in LEAP-4 as the TSL model (www.lin-Note 5 *earx.com*), involving parameters K_{TM} , E_{TM} , K_{XM} , and E_{XM} . This more accurate transducer model is described in a technical paper <u>here at our web site</u>. After-burn-in specifications are measured 12 hours after exiting the transducer by a continuous sine wave for 2 hours. The sine wave frequency equals the transducer Fs, at level 15 VRMS (FR055WA05), 19 VRMS (FR084WA03). Note 6 Units are not burned in before shipping.

Specifications are subject to change without any further notice. Copyright © 2022 by Wavecor Ltd., China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd. For more information please visit www.Wavecor.com








FR055WA05 2" / FR084WA03 3¼" 64 oh

64 ohm fullranges for Line Arrays


HARMONIC DISTORTION



Measuring conditions, Harmonic Distortion Driver mounting: In sealed, heavily stuffed enclosure, internal volume 0.5 lit. (FR055WA05) / 1.0 lit. (FR084WA03). Microphone distance: 0.5 m Input signal: Stepped sine wave, 5.1 VRMS (FR055WA05) / 8.0 VRMS (FR084WA03)

Smoothing: 1/6 oct.

Harmonic Distortion




Specifications are subject to change without any further notice. Copyright © 2022 by Wavecor Ltd., China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd. For more information please visit <u>www.Wavecor.com</u>




FR055WA05 2" / FR084WA03 3¼"

64 ohm fullranges for Line Arrays


OUTLINE DRAWING (nominal dimensions)





June 6, 2022

CONNECTIONS



Terminal thicknes: 0.5 mm Terminal plating: Gold

PACKAGING AND ORDERING INFORMATION

Part no. FR055WA05-01	64 ohm, packed in pairs
Part no. FR055WA05-02	64 ohm, packed in bulk (industrial) packaging
Part no. FR084WA03-01	64 ohm, packed in pairs
Part no. FR084WA03-02	64 ohm, packed in bulk (industrial) packaging

Latest update: June 6, 2022

Specifications are subject to change without any further notice. Copyright © 2022 by Wavecor Ltd., China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd. For more information please visit www.Wavecor.com